

Corken Autogas Pumps

CORKEN

The Corken Autogas Pump achieves new levels of performance with higher flow at high differential pressures, non-pulsating and quiet transfer, longer pump life and a design that is easy to repair. The pump is also versatile enough to be used in like applications such as cylinder filling, vaporizer feeding or bulk transfer.



bergquistinc.com | 800 537 7518



Frame mount shown
C-Face mount also available.

FF-150 Coro-Flo Model

Model No	Description	Inlet	Outlet	RPM	Working Pressure	Differential Pressure
FF075	Bare pump	1 1/2" ANSI 300# RF Flange	1" ANSI 300# RF Flange	3450	400 psig	150 psig
FF075CD6A-101-14(213)	Pump on direct drive mount 213T baseplate - no motor					
FF075CD6A-101-14-7.5 HP	Pump on direct drive mount baseplate with 7.5 hp motor					
FF150¹²³	Bare pump					250 psig
FF150CD6A-101-14 (184) ¹²³	Pump on direct drive mount 184T baseplate - no motor					
FF150CD6A-101-14 (213) ¹²³	Pump on direct drive mount 213T baseplate - no motor					
FF150CD6A-101-14 ¹²³	Pump on direct drive mount 215T baseplate and 10 HP motor					
HDPFF075-1P75¹³⁴	Pump on direct drive mount with bypass and 7.5 HP motor. Includes Variable Frequency Drive					
HDPFF075-3P75¹³	Pump on direct drive mount with bypass and 7.5 HP motor.					

Notes

- (1) All pumps require companion flange kit (part no 6133X1) which includes bolts, nuts, flexitalluc gaskets and flanges
- (2) Use B166B-CAUY bypass with 100 - 225 psi spring range (150 max allowed per NFPA 58)
- (3) Switch not included. Requires 3 phase explosion proof switch with magnetic starter
- (4) Variable frequency drive converts single phase to three phase service, also has slow start up function which helps nuisance excess flow closures and allows for switch without magnetic starter